

# BUILD THE OPTIMUM EMERGENCY EYEWASH SETUP

## SE4045 EMERGENCY EYEWASH STATION

### 45 LITRE EYEWASH STATION

- Delivers at least 15 minutes of non-Injurious flow to meet the AS 4775 - 2007 standard
- One-step activation for near instantaneous flow
- Manifold and base work together to capture wastewater and drain into disposal bin or cart
- MIN and MAX lines on manifold help ensure proper water level
- Front-facing opening to easily add water and preservative
- Hi-vis green color is easily recognizable if an injury occurs
- Gravity-fed station can be wall mounted, used with a stand, or placed on a table/cart
- Includes a wall bracket, potable water preservative, test log card and drainage hose

Eyewash station, stand, drain cart, alarm and dust cover sold separately



## SE4045CART

### DRAIN CART

- Strong plastic construction with 60 Litre capacity
- Small drain hose opening in top to collect water
- Screw-on cap to cover drain hose opening when rolling filled cart
- Ergonomic design for easy pushing or pulling to disposal area
- Drain cap at bottom of cart is easily unscrewed for wastewater disposal and can accommodate standard water hose
- Molded wheels and steel axle for stability and durability on range of surfaces



## SE4045STAND

### EYEWASH TANK STAND

- Designed for 45 Litre Eyewash Tanks
- Ensures station is at AS 4775 required height for operation
- Simple six-bolt assembly with included hardware
- Can be used in and easily moved to varied locations
- Durable powder-coated steel construction
- Open base for wastewater disposal cart or container
- Rubber feet for stability



## EMERGENCY EYEWASH STATION ALARM #SE4045ALARM

The optional alarm system adds another level of safety to the emergency eyewash station. When the station is activated, the alarm automatically alerts nearby workers that help is needed with a siren and flashing light. \* Batteries NOT Included.



Mounts neatly on top of Emergency Eyewash Tank.

## DUST COVER #SE4045COVER



- Protects eyewash station from dust and environmental contaminants
- Maintains useability with hook and loop closure that releases with activation of tray

